



P.Δ.Easy Environmental Sensor

Part Number – YSBSC03660



The P.Δ.Easy environmental sensor enables any intelligent building project to precisely measure a variety of essential environmental parameters including PIR occupancy, ambient light, temperature, CCT colour, humidity, light flicker, VOC gases and ambient noise levels.

The ceiling recessed PoE sensor can be powered by standard 802.3at Class 1 PoE network switches enabling easy and rapid installation without the need of certified electricians. Simply, decide the sensor position and connect it using standard Cat6/6A structured cabling to build a comprehensive intelligent building sensor network.

Each multi-sensor provides Bluetooth connectivity for enhanced beacon marketing services or to enable tracking and wayfinding applications without the need for separate beacons with battery replacement maintenance. All functions may be programmed/controlled or commissioned using a standard BLE network.

The multi-sensor features advanced movement detection coverage of up to 6m depending on installation height with PIR detection optimised for superior performance. The PIR feature may be set in absence or presence detection mode with fully flexible programmable timing. The daylight feature is used to maintain constant light level where controlled luminance (daylight linking) is required.

The inbuilt temperature and humidity sensor ensure that building thermal mapping can be undertaken within zones, rooms, floors and complete buildings for extra levels of comfort and safety.

For circadian lighting applications an advanced colour sensor is included to provide assurance that an installation is meeting the Well Building V2 standard.



Product description

Main Features

- Advanced Pyro technology offers excellent sensitivity to small movements
- Full 360° detection area
- Allows advanced daylight harvesting
- Connection via standard PoE RJ45 connectors
- Bluetooth communication and beacon functions
- Allows integration with building systems for climate control possibilities.
- Ambient noise measurement provides dual assurance excess noise levels are not reached or to determine excess noise events in zones.
- A sophisticated digital gas sensor opens new possibilities for the measurement of indoor air quality and VOC gases including CO2
- Construction: Injection moulded polycarbonate UL94 V0 rated.
- Fixing: Moulded retainer ring
- Mounting hole diameter: 45 to 50mm diameter
- Weight: 70g
- Temperature: 0 to 45°C
- Humidity: 15 - 85% RH (non-condensing)
- Supply: Standard 802.3at
- Typical PIR stability time: 7 seconds from system switch on
- Power consumption: <1W
- Sensor dimensions:
 - Diameter front cover: 67mm
 - Length tube: 100mm
 - Diameter tube: 44mm
 - Overall length: 116mm

Application Environment

- Hospital ward
- Consulting room
- Open plan office
- Partitioned office
- Seminar room
- Small workshop
- Studio space
- Storage room
- Corridor
- Reception area
- Retail outlets
- Restaurant
- Library aisle
- Public library
- Classroom
- IT facilities
- Atrium
- Staircase area
- Hotel lounge
- Lecture theatre
- Rest room
- Galleries
- Exhibition area
- Adaptable spaces

© PRYSMIAN GROUP 2021, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by Prysmian.