


Draka UC Connectivity

Draka Cat6a Screened Keystone Jack – Silver

Part Number - YMJBPO3208

Overview



- Plastic Free Eco-Packaging – Pack of 24
- Supports 10 Gigabit Ethernet
- Suitable for POE++ applications IEEE 802.3bt Type 4
- 180° IDC to Jack – Tool Free Design
- High quality die cast housing
- Mounts in both patch panel and shuttered adaptor
- Supplied with dust cover and nylon cable tie
- 3rd Party Verification



Product Description

Draka Cat6a STP keystone jacks are designed to meet and exceed Cat6a performance according to latest ISO and TIA standards. The fully shielded die-cast body of the keystone jack is robust, as well as offering outstanding performance in eliminating alien crosstalk. Suitable for mounting in 1U/19" modular patch panel or a faceplate in conjunction with a Euro or LJ6C sized shuttered adaptor, these jacks are quick and easy to install making them a great choice for all data installers.

Product Specification

Type of Connector	Jack RJ45 8P8C
Category	Cat6a
Connection Type	Tool Free Design
Colour	Silver
AWG Range	22~26
Width	14.66mm
Depth	38.05mm

© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Height	19.30mm
Suitable for cable types	Solid Core / Round / S/FTP, F/FTP, U/FTP, F/UTP
Housing	Zinc Alloy
RJ45 Contact	Phosphor Bronze with 50u" gold plating
IDC Contacts	Phosphor Bronze with Tin plated
Plug Insertion Life	Min 750 Insertions
Contact Force	100 Grams with FCC Compliant Plug
Plug Retention Force	50N (11lbs) for 60s ±5s
Suitable Tool	No specific tool required
Operating Temperature Range	-10°C to 60°C
Storage Temperature Range	-40°C to 70°C

Electrical Specification

Insulation Resistance	500MΩ
Dielectric Withstanding Voltage	1000V AC
DC Current Rating	1.5A
DC resistance	0.1Ω max
Contact Resistance	20mΩ

© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Standards Complied

ISO/IEC 11801-1:2017 (Ed 1.0)	Information technology - Generic cabling for customer premises: Part 1 General Requirements
ISO/IEC 11801-2: 2017 (Ed. 1.0)	Information technology — Generic cabling for customer premises — Part 2: Office premises
EN 50173-1:2018 (Ed 1.0)	Information technology. Generic cabling systems - General requirements
EN 50173-2:2018 (Ed 1.0)	Information technology. Generic cabling systems - Office premises
IEC 60603-7-51: 2010 (Ed. 2.0)	Connectors for electronic equipment - Detail specification for 8-way, shielded, free and fixed connectors, for data transmissions with frequencies up to 500 MHz
IEC 60512-99-002: 2019 (4PPoE)	Connectors for electrical and electronic equipment - Tests and measurements - Part 99-002: Endurance test schedules - Test 99b: Test schedule for unmating under electrical load
TIA-568.2-D: 2018	Balanced Twisted-Pair Telecommunications Cabling and Components Standards
RoHS	Restriction of Hazardous Substances Directive 2011/65/EU & 2015/863/EU
REACH	Regulation (EC) No 1907/2006 - Registration, Evaluation, Authorisation and Restriction of Chemicals EC1907/2006




© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Draka UC Connectivity

Product Drawings



© PRYSMIAN GROUP 2020, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian.